C2G

10ft (3m) 18 AWG Outlet Saver Power Extension Cord (NEMA 5-15P to NEMA 5-15R) (TAA Compliant)

Part No. 03116



This outlet saver cord keeps your surge strip and UPS outlets from being blocked by bulky AC transformers. It is designed to work with power transformers, computers, monitors, scanners, printers, and other devices that use the 3-pin male-to-female shroud power connector. Plus this heavy duty 18 AWG cord features a fully molded design for maximum durability and long life.

The female connector plugs directly into the device power cable while the male connector plugs into a standard outlet.

Features & Benefits

- Extend powered devices away from wall outlets
- Durable, heavy-duty construction
- Available up to 25ft

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120031161	Country Of Origin	Taiwan, Province Of China
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Power Cord		

Dimensions

Product Length US	10.0 FT

Trade Programs

TAA Compliant	Yes

Technical Information

Wire Gauge	18 AWG	Jacket Rating	SVT Rated
Amperage	10 A	Connector 2	NEMA 5-15 Male
Connector 1	NEMA 5-15 Female	Voltage	125.0 V

Downloaded from Arrow.com.