



+ CONNECTORS
RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
JACK,RTANG,PCB,75 OHM,BNC
Miniature Coax | [OCM](#) , [PCF](#)

5415373-1
TE Internal Number: 5415373-1

[EU RoHS Compliant with Exemptions](#)
[EU ELV Compliant with Exemptions](#)

Connector Interface BNC
Connector Style Jack
Mated Outer Diameter (Approximate) 14.529 mm [.572 in]
Impedance (Ω) 75
Number of Positions 1

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings
JACK, PCB, RIGHT ANGLE, 75 OHM, BNC
PDF ([TIFF AVAILABLE](#))
English

CAD Files
3D PDF
PDF
3D
Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

BNC PCB Straight And Right Angle Connectors

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface BNC

Connector Style Jack

Sealable No

Connector & Contact Terminates To Printed Circuit Board

Configuration Features

Number of Positions 1

PCB Mounting Orientation Right Angle

Electrical Characteristics

Impedance (Ω) 75

Body Features

Body Material Zinc

Body Plating Material Tin

Body Insulation Without

Contact Features

Center Contact Plating Material Gold

Center Contact Material Beryllium Copper

Center Contact Plating Thickness (μin) 30

Mechanical Attachment

Connector Mounting Type Panel

Panel Attachment Style Rear Mount

PCB Mount Retention Type Hold-Down Posts

PCB Mount Retention With

Dimensions

Mated Outer Diameter (Approximate) 14.529 mm [.572 in]
Height above PCB 10.97 mm [.432 in]
Mounting Post Length 4.34 mm [.171 in]

Packaging Features

Packaging Method Carton

Other

Dielectric Material Polymethylpentene
Grade Commercial

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF