



Part Number : [193230001](#)

Product Description : VersaKrimp Metric Ring Terminal for M2.5 Stud Size (#4), Un-insulated, Bag

Series Number : 19323

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : AA1-332-M2,5

Documents & Resources

Drawings


[Drawing 193230001_sd.pdf](#)

3D Models and Design Files

[3D Model 193230001_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19323
Description	VersaKrimp Metric Ring Terminal for M2.5 Stud Size (#4), Un-insulated, Bag
Keyword	Ring Terminal, Ring Terminals
Product Family	Metric Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	887191289151

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.465/g
Packaging Type	Bag
Stud Size	M2.5
Wire Size (AWG)	N/A
Wire Size mm ²	0.50-1.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
-------------	-------------

PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

This document was generated on Jul 29, 2024