






NOTES:

ELECTRICAL

1. VOLTAGE RATING : 30 VDC RMS
2. CURRENT RATING :0.5AMP MAX PER CONTACT
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 1000 MEGOHMS MIN @ 500 VCD
5. WITHSTANDING VOLTAGE : 500 VAC RMS 60Hz , 1MIN
6. OPERATING : 10000 CYCLES MIN

MECHANICAL :

1. HOUSING MATERIAL : NYLON, UL94V-0
HOUSING COLOR : BLACK
2. CONTACT MATERIAL : PHOSPHOR BRONZE 0.20mm THICKNESS
3. PLATING : 30u" GOLD PLATING OVER NICKEL
4. SHIELD MATERIAL : COPPER ALLOY 0.50mm THICKNESS
5. PLATING : 50u" NICKLE

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C
2. OPERATION : -40°C TO +85°C
3. WAVE SOLDERING TEMPERATURE : 255°C ~265°C (5~10 SECONDS)
4. RoHS COMPLIANT.

DETACHED LISTS	MM (INCH) TOLERANCES EXCEPT AS NOTED <table> <tr> <td>MM</td> <td>±</td> </tr> <tr> <td>.0 ± 0.2</td> <td>±</td> </tr> <tr> <td>.00 ± 0.15</td> <td>±</td> </tr> <tr> <td>.000 ± 0.075</td> <td>±</td> </tr> </table>	MM	±	.0 ± 0.2	±	.00 ± 0.15	±	.000 ± 0.075	±	RoHS Compliant			
	MM	±											
	.0 ± 0.2	±											
	.00 ± 0.15	±											
.000 ± 0.075	±												
THIRD ANGLE PROJECTION THIRD ANGLE PROJECTION THIRD ANGLE PROJECTION	TITLE HDMI CONNECTOR(SMT TYPE)												
DFTO Cathy DATE 08/10/2006		DRAWING NO. CE813028-LA /PART NO. SEE TABLE		SIZE A3	REV 0								
SCALE : 3:1			DO NOT SCALE DRAWING		SHEET 1 OF 1								

PART NUMBER
E810K-SBY104-L