Quick Reference

Search by part #

Check distributor part inventory

Products

Browse Products

-By Device -

-By Product Line-

-Attachment Methods

-Interface Materials-

-Accessories -

Useful Links

MSDS Safety Sheets
How to Order?
Find Sales Rep
Find Distributor
Sample Request
Quote Request
Catalog Request
Building a Part #
Part # Cross Ref

Accessories

Standard Mounting Pads

The following Mounting Pads are for use with Integrated Circuits

7717-21DAPG


RoHS Compliant | Product Change Notice

(DAP)

Leads: 10

Outside Diameter mm (in): 12.70 (0.500)

Thickness: 6.99 (0.275)



7717-21NG


RoHS Compliant | Product Change Notice

(nylon)

Leads: 10

Outside Diameter mm (in): 12.70 (0.500)

Thickness: 6.99 (0.275)



7717-19DAPG


RoHS Compliant

(DAP)

Leads: 8

Outside Diameter mm (in): 12.70 (0.500)

Thickness: 6.99 (0.275)



7717-19NG


RoHS Compliant

(nylon)

Leads: 8

Outside Diameter mm (in): 12.70 (0.500)

Thickness: 6.99 (0.275)



7717-107NG


RoHS Compliant

(nylon)

Leads: 8

Outside Diameter mm (in): 10.92 (0.430)

Thickness: 3.30 (0.130)



7717-156DAPG


RoHS Compliant | Product Change Notice

(DAP)

Leads: 14

Outside Diameter mm (in): 19.05 x 11.43 (0.750 x 0.450)

Thickness: 1.27 (0.050)



7717-156NG


RoHS Compliant | Product Change Notice

(nylon)

Leads: 14

Outside Diameter mm (in): 19.05 x 11.43 (0.750 x 0.450)

Thickness: 1.27 (0.050)



7717-8DAPG


RoHS Compliant | Product Change Notice

(DAP)

Leads: 8

Outside Diameter mm (in): 9.53 (0.375)

Thickness: 1.91 (0.075)



7717-8NG


RoHS Compliant | Product Change Notice

(nylon)

Leads: 8

Outside Diameter mm (in): 9.53 (0.375)

Thickness: 1.91 (0.075)



7717-122DAPG


RoHS Compliant | Product Change Notice

(DAP)

Leads: 8

Outside Diameter mm (in): 9.27 (0.365)

Thickness: 1.78 (0.070)



7717-122NG


RoHS Compliant | Product Change Notice

(nylon)

Leads: 8

Outside Diameter mm (in): 9.27 (0.365)

Thickness: 1.78 (0.070)



7717-107DAPG


RoHS Compliant

(DAP)

Leads: 8

Outside Diameter mm (in): 10.92 (0.430)

Thickness: 3.30 (0.130)



7717-30NG


RoHS Compliant

(nylon)

Leads: 10

Outside Diameter mm (in): 9.53 (0.375)

Thickness: 1.91 (0.075)



7717-30DAPG


RoHS Compliant

(DAP)

Leads: 10

Outside Diameter mm (in): 9.53 (0.375)

Thickness: 1.91 (0.075)



7717-6NG


RoHS Compliant

(nylon)

Leads: 6

Outside Diameter mm (in): 9.53 (0.375)

Thickness: 1.91 (0.075)



7717-6DAPG


RoHS Compliant

(DAP)

Leads: 6

Outside Diameter mm (in): 9.53 (0.375)

Thickness: 1.91 (0.075)



Downloaded from Arrow.com.