650V 25A Field Stop Trench IGBT - RGW50TS65 (New)

The datasheet is coming soon.

Package

VIEW

BUY * SAMPLE * FAQ CONTACT US

* This is a standard-grade product.
For Automotive usage, please contact Sales.

PRODUCT DETAIL | TECHNICAL DOCUMENTS

PART NUMBER | **RGW50TS65GC11**
STATUS | **ACTIVE**
PACKAGE | **TO-247N**
UNIT QUANTITY | **450**
MINIMUM PACKAGE QUANTITY | **30**
PACKING TYPE | **TUBE**
ROHS | **YES**

SPECIFICATIONS:

Series	W: High speed fast SW
V_{CES} [V]	650
I_C(100°C)[A]	25
$V_{CE(sat)}$ (Typ.) [V]	1.5
tf(Typ.) [ns]	53
BV_{CES} (Min.)[V]	650
Storage Temperature (Min.) [°C]	-55
Storage Temperature (Max.) [°C]	175

FEATURES:

N/A

RELATED PRODUCTS Other New/Updated Products Relating to RGW50TS65

PART NUMBER	Product Series	Datasheet	Distribution Inventory
RGT20NL65D	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRY

Downloaded from Arrow.com.

PART NUMBER	Product Series	Datasheet	Distribution Inventory
RGT20NS65D(LPDS)	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRY
RGWX5TS65	650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch	-	INQUIRY
RGWX5TS65D	650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch	-	INQUIRY
RGT20NS65D(TO-262)	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRY
RGT20TM65D	650V 10A Field Stop Trench IGBT		INQUIRY

NEW PRODUCT LIST

Downloaded from Arrow.com.