





REVIEWS			
REV	DESCRIPTION, EON, EAR NO.	DATE	APP'D
A	PROPOSAL	MAR31/16	LCHAN
B	REVISE THE NOTES	FEB 24/17	LCHAN



RECOMMENDED PANEL CUTOUT



MATERIALS:


PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0. COLOUR BLACK.

CONTACT: PHOSPHOR BRONZE.

CONTACT PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES.
SEE PART NO. FOR THICKNESS.
50u" [1.27 MICRONS] MIN. NICKEL UNDERPLATE.
100u" [2.54 MICRONS] MIN. MATTE-TIN ON CONTACT TAILS.

AMPHENOL PART NUMBER: RJE1J-166-0X10

- Gold plating:
0. gold plating (1~3u")
 1. 6u" gold plating
 2. 15u" gold plating
 3. 30u" gold plating
 4. 50u" gold plating



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)
PCB THICKNESS: 1.57MM
TOLERANCE: +/-0.05MM

UNLESS SPECIFIED OTHERWISE		DRAWN	FRANK W	MAY16/14	Amphenol Canada Corp.	
PRIMARY UNITS	MILLIMETERS	CHECKED	LCHAN	MAY16/14		
SECONDARY		ME APP'D			MODULAR JACK, SINGLE PORT, VERTICAL MOUNT, 6P6C, WITHOUT SHIELD. TRAY PACKAGING - RoHS COMPLIANT	
REFERENCE IN PARENTHESES		Q.A. APP'D				
GENERAL TOLERANCES		DWG APPR.				
1 DECIMAL PLACE	±0.38	ENG. REL. NO.				
2 DECIMAL PLACES	±0.20	REF.				
3 DECIMAL PLACES		THIRD ANGLE PROJECTION				
ANGULAR DEGREES	±1.0 °	DO NOT SCALE DRAWING				
					DWG. NO.	REV B
					P-RJE1J-166-0X10	
					CODE ID NO.	03554
					DWG SIZE:	X
					SCALE:	4:1
					SHEET	1 OF 2

