


REV. 5 8/25/98

COIL: @ 25°C

RESISTANCE	1600 OHMS ± 10%
NOMINAL VOLTAGE	18.0 VDC
MUST OPERATE	9.8 VDC
MUST RELEASE	0.92 VDC

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX
RELEASE TIME 2.0 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. R.B. 5/29/97 CK. Jerry C 8/25/98

COMMUNICATIONS INSTRUMENTS, INC.

CUST. C. I. I.
CUST. NO. COTS STD.

TYPE PRMGS RELAY

PRMGSC-18XW

SUPERSEDED
NOT the LATEST REVISION

Downloaded from Arrow.com.