Part Number : 734205190
Product Description : SMP-MAX Plug, Straight, Smooth Bore, Panel Mount, Threaded, 5.00mm Length, Tri-Metal Plating, One Piece Per Bag, 50 Ohms
Series Number : 73420
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

734205190_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/30/2017 (7 July 2017)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73420
Description	SMP-MAX Plug, Straight, Smooth Bore, Panel Mount, Threaded, 5.00mm Length, Tri-Metal Plating, One Piece Per Bag, 50 Ohms
Application	Telecommunications/Networking, RF
Product Name	SMP-MAX
Style	Panel
Type	Subminiature
UPC	887191124438

Electrical

Frequency	10 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 330 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Plug
Keying to Mating Part	N/A
Net Weight	8.705/g
Orientation	Straight

Downloaded from Arrow.com.

Packaging Type	Individual Bag
Panel Mount	Yes
Panel Mount Method	Thread-In
PCB Mounting	Round Post
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Downloaded from Arrow.com.