

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=HR36308000J0G* > HR36308000J0G

HR36308000J0G

HR36308000J0G - Terminal Blocks : Spring clamp, 5.08mm pitch, 45 degree wire-inlet, 3-level, parallel type , 36 position



ACTIVE

Distributor Stock

Customer drawing

Environmental Compliance Report

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications

Download document

General	Dimensional	Electrical	Physical	Approvals / Certifications	Mounting
General					
Packaging	Box				
Product Type	Spring Clamp System				
Series	HR				
Number of Positions	36				
Dimensional					
Strip length (Wire)	5 to 6 mm				
Solid wire size (AWG)	12 to 28				
Stranded wire size (AWG)	12 to 28				
Pitch	5.08 mm				
Electrical					
Withstanding Voltage	1.6 kV				
Current rating	10 A				
Voltage rating	300 V				
Physical					
Soldering temperature (celcius)	260 +/- 5 Celcius (5 sec)				
Color (Housing)	Grey				
Conductor entry angle	45°				
Material (Housing)	Thermoplastic UL94V-0				
Terminal material	Brass				
Terminal plating	Tin				
Connection Type	Spring connction				
Temperature (Operating - range)	-40 to 115 Celcius				
Approvals / Certifications					
Approvals / Certifications	cULus				
Mounting					
Board attachment	TMT				

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.