

Part Number : 1062831010
Product Description : Quad Small Form-factor Pluggable (QSFP) Optical Jumper Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP Multimode 50/125µm 3.00mm Round Cable Plenum, High Bandwidth (OM3), 10.0m (32.81') Length, Aqua Cable
Series Number : 86004
Status : Active
Product Category : Fiber Optic Cable Assemblies

Documents and Resources

Drawings

1062831010_sd.pdf

Specifications

1062840501-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Decabromodiphenylether; Diphenyl(2,4,6-trimethylbenzoyl)phosphine oxide; 2-Methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one... per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86004
Description	Quad Small Form-factor Pluggable (QSFP) Optical Jumper Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP Multimode 50/125µm 3.00mm Round Cable Plenum, High Bandwidth (OM3), 10.0m (32.81') Length, Aqua Cable
Connector to Connector	MTP-to-MTP
Mode	Multimode Enhanced
Product Name	MTP,QSFP Plus,QSFP+
UPC	822350973991

Agency

CSA	LR64395
UL	E72548

Physical

Boot Type	Straight
Cable Length	10.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm

Downloaded from Arrow.com.

Net Weight	98.170/g
Single Ended	No
Wire/Cable Type	OM3 Plenum

Downloaded from Arrow.com.