

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 13A, 120V, 16 AWG, 15 ft. (4.57 m), Black

MODEL NUMBER: P024-015-13A



15 ft. extension cord with 5-15P and 5-15R connectors connects bulky power transformers without blocking adjacent outlets on your PDU.

Features

15-ft. (4.57 m) Extension Cord Connects PCs, Printers, Monitors and Other Equipment This cord is recommended for home/office desktop computer applications, home theater setups or other applications where multiple devices are plugged into a surge protector, PDU or UPS system. It allows you to connect bulky power adapters to a NEMA 5-15R outlet without blocking adjacent outlets. The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 15-ft. (4.57 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 15-ft. (4.57 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P024-015-13A 15-ft. (4.57 m) Extension Cord, NEMA 5-15P to NEMA 5-15R, Black

Specifications

OVERVIEW	
UPC Code	037332197153
Product Type	PDU Extension Power Cord
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
Connector Style	Straight



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.5mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Power Cord Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57
Cable Length (cm)	457.20
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 10.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 25.40
Shipping Weight (lbs.)	1.17
Shipping Weight (kg)	0.53
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.