

Honeywell Pricebook - EMEA



**Solutions that
Enable Productivity**

Honeywell

Product Access Policy

Products on the pricelist are now classified in five categories: A, B, C, Virtual and New. These categories have been in place for legacy HSM products since 2013; the same categorization is now being introduced to legacy Intermec products. **Please note that for legacy Intermec products, the conditions and associated leadtime changes will not come into effect until October 2015; the classification indicated in the Pricelist is for information only at this time.**

For more easy understanding these categories carry in the Price List a corresponding color.

The categories reflect our high runners (A), medium runners (B) and low runners (C). These classifications will set clear expectations on the Lead Time and will increase our ability to meet the first promise dates.

The category Virtual is connected to our Service Contracts and Software products for which the aimed delivery is depending on the delivery of the hardware or is more a virtual transaction of the software key or contract. We are aiming to complete the virtual transaction within 3 working days.

The category New is referring to new products which will be assigned an ABC classification between 3-6 months after release, when the market trends have been reviewed and an ABC classification can be allocated per product item.

Media remains outside the scope of this categorization at this time.

The Pricelist with A, B, C, Virtual and New classifications is available on the Partner Web.

With the upcoming changes the aim is to deliver the following:

- Increased accuracy of our delivery dates.
- Better aligned Lead Times for core products and accessories considered as high and medium runners. Visibility on high/low runners, Visibility on made to order/ tailor made products (C category items), Visibility on non returnable & non cancellable (C category items).
- Quarterly review of classifications based on ordering pattern, market trends & product lifecycle.
- On a weekly basis a Lead Time map will be shared, providing you with updates on the exceptions in our supply chain including extended leadtimes and exceptional demand quantities.
- Please note: C items will be supplied within factory Lead Time and are non returnable.
- For all future orders a minimum order value is applicable. In case your sales order is not meeting the required minimum value, it still will be processed, but an administration fee will be added. You can find the minimum order value and corresponding fee on the pricelist on the partner web. Orders for demo units, Software, Service Contracts and OEM engines do not require a minimum value.
- Please ensure your purchase order specifies clearly when you have a requested delivery date that deviates from our published leadtimes.
- Amendments to orders will be accepted only within 24 hours after reception of the Order Acknowledgment.
- All cancellation requests are subject to approval and Honeywell reserves the right to charge additional fee with the minimum 10% of the ordered goods.

Scanning

Including cables and accessories

A	15 working days
B	15 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

Printing

Including cables and accessories

A	15 working days
B	20 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

Mobility, Supply Chain

Including cables and accessories

A	30 working days
B	30 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

RFID

Including cables and accessories

A	30 working days
B	30 working days
C	Factory Lead Time
New	Factory Lead Time
Virtual	not applicable (related to Software and Service Contracts)

Intermec Computers - CN51 Mobile Computer

CN51 base configuration includes 1.5 GHz TI OMAP4470 Dual Core, Multi-Engine Processor, 1 GB RAM, 16 GB Flash Memory, SmartSystems(tm) Provisioning Client, WLAN, Bluetooth, and Battery Pack. Options include choice of Operating System (Microsoft WEH 6.5 or Android 4.1), Keypad, WWAN (includes GPS), Imager, and Camera. Also available without WWAN Radio, Imager, or Camera.

WWE = English Only

LP = Language Provisioned. At power up, user must select English, Spanish, German, Italian, French, Russian, Traditional Chinese, Simplified Chinese, or Korean. This cannot be changed after it is selected.

Required Accessories: AC Power Supply or Docking systems for charging and associated power supplies. Users Manuals available via Download.

Hardware - Printers

SKU	SKU Type	SKU Description	List (€)
200540-100	N	CN51 PrintPAD, RS232, Bluetooth, E-Charge	1182.89
200541-100	N	CN51 PrintPAD, RS232, Bluetooth, DEX, Magnetic Card Reader, E-Charge	1481.60

Hardware - Standard Config - Android

SKU	SKU Type	SKU Description	List (€)
CN51AN1KC00A1000	B	CN51 / Numeric / EA30 Standard Range Imager / Camera / 802.11 a/b/g/n / Bluetooth / Android 4.2.2 / All Languages	1985.79
CN51AN1KC00A2000	N	CN51 / Numeric / EA30 Standard Range Imager / Camera / 802.11 a/b/g/n / Bluetooth / Android 6.0 / All Languages	2028.79
CN51AN1KCU2A1000	A	CN51 / Numeric / EA30 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 4.2.2 / All Languages	2332.11
CN51AN1KCU2A2000	N	CN51 / Numeric / EA30 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 6.0 / All Languages	2375.11
CN51AN1KN00A1000	C	CN51 / Numeric / EA30 Standard Range Imager / No Camera / 802.11 a/b/g/n / Bluetooth / Android 4.2.2 / All Languages	1812.63
CN51AN1KN00A2000	N	CN51 / Numeric / EA30 Standard Range Imager / No Camera / 802.11 a/b/g/n / Bluetooth / Android 6.0 / All Languages	1855.63
CN51AN1SCU2A1000	B	CN51 / Numeric / EA31 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 4.2.2 / All Languages	2286.60
CN51AN1SCU2A2000	N	CN51 / Numeric / EA31 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 6.0 / All Languages	2329.60
CN51AQ1KC00A1000	C	CN51 / QWERTY / EA30 Standard Range Imager / Camera / 802.11 a/b/g/n / Bluetooth / Android 4.2.2 / All Languages	1985.79
CN51AQ1KC00A2000	N	CN51 / QWERTY / EA30 Standard Range Imager / Camera / 802.11 a/b/g/n / Bluetooth / Android 6.0 / All Languages	2028.79
CN51AQ1KCU2A1000	B	CN51 / QWERTY / EA30 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 4.2.2 / All Languages	2332.11
CN51AQ1KCU2A2000	N	CN51 / QWERTY / EA30 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 6.0 / All Languages	2375.11
CN51AQ1SCU2A1000	B	CN51 / QWERTY / EA31 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 4.2.2 / All Languages	2286.60
CN51AQ1SCU2A2000	N	CN51 / QWERTY / EA31 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / Android 6.0 / All Languages	2329.60

Hardware - Standard Config - Windows

SKU	SKU Type	SKU Description	List (€)
CN51AN1KC00W0000	B	CN51 / Numeric / EA30 Standard Range Imager / Camera / 802.11 a/b/g/n / Bluetooth / WEH 6.5 / WW English	1985.79
CN51AN1KCU2W1000	A	CN51 / Numeric / EA30 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / WEH 6.5 / WW English	2332.11
CN51AN1KCU2W3000	B	CN51 / Numeric / EA30 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / WEH 6.5 / All Languages	2332.11
CN51AN1KN00W0000	B	CN51 / Numeric / EA30 Standard Range Imager / No Camera / 802.11 a/b/g/n / Bluetooth / WEH 6.5 / WW English	1812.63
CN51AN1KN00W2000	B	CN51 / Numeric / EA30 Standard Range Imager / No Camera / 802.11 a/b/g/n / Bluetooth / WEH 6.5 / All Languages	1812.63
CN51AN1SCU2W3000	A	CN51 / Numeric / EA31 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / WEH 6.5 / All Languages	2286.60
CN51AQ1KC00W0000	C	CN51 / QWERTY / EA30 Standard Range Imager / Camera / 802.11 a/b/g/n / Bluetooth / WEH 6.5 / WW English	1985.79
CN51AQ1KCU2W1000	A	CN51 / QWERTY / EA30 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / WEH 6.5 / WW English	2332.11
CN51AQ1KN00W0000	C	CN51 / QWERTY / EA30 Standard Range Imager / No Camera / 802.11 a/b/g/n / Bluetooth / WEH 6.5 / WW English	1812.63
CN51AQ1SCU2W3000	C	CN51 / QWERTY / EA31 Standard Range Imager / Camera / 802.11 b/g/n / Bluetooth / UMTS/HSPA / GPS / WEH 6.5 / All Languages	2286.60

Accessories - Accessories

SKU	SKU Type	SKU Description	List (€)
220262-102	N	Kit, Charging Vehicle Mount Bracket, PrintPAD MC65/67, CN70, 99EX	169.27
220267-101	N	Kit, 5-Up E-Charge Settlement Room Bracket, PrintPAD CN3/4/3e/4e, MC70/75, 99EX (For use with E-Charge Option)	537.68

Accessories - Batteries

SKU	SKU Type	SKU Description	List (€)
318-052-011	A	Battery Pack, CN51, 3.9Ah Li-Ion (Spare or replacement battery pack for CN51 (one pack included with each mobile computer))	113.22
318-052-021	N	Battery Pack,CN51,Li-Ion,TW 2014 Comp.	113.22

Accessories - Battery Chargers

SKU	SKU Type	SKU Description	List (€)
852-068-011	C	Battery Charger, Quad CN50	287.49

Accessories - Chargers

SKU	SKU Type	SKU Description	List (€)
220515-100	N	AC Adapter for Charging with U.S. plug	41.82

Accessories - Comm Dock Accys

SKU	SKU Type	SKU Description	List (€)
871-238-011	B	Ether Mod, Single Dk-FlexDk/CN3/CN50/CN51/CK3 (replaces 871-025-101)	113.22
871-238-012	N	Ether Mod, Single Dk-FlexDk/CN3/CN50/CN51/CK3 (replaces 871-238-011)	113.22

Accessories - Common Cables

SKU	SKU Type	SKU Description	List (€)
210191-101	N	Cable DB-9 F (7' /2.1m)	42.82
210267-100	N	Cable, Right Angle, USB	30.87

Accessories - Communication Docks

SKU	SKU Type	SKU Description	List (€)
871-032-102	A	CN50 Multi-Dock, Charge Only (4-Bay Dock. Requires AC Adapter (851-082-205 everywhere except EMEA; 851-095-131 is required for CN50 use in EMEA) and country specific power cord.)	358.00
871-032-201	A	Multi-Dock, CN50/ CN51 Ethernet	615.00
871-033-021	A	CN50/CN51 Desktop Single Dock, RoHS	210.00

Accessories - Data Cables

SKU	SKU Type	SKU Description	List (€)
236-209-001	B	Cable Assy, USB-A to USB-microB, 1M (Used with CN50/CN51 Desktop Adapter (851-093-101/201) to PC USB port enabling quick data transfer.)	29.97
321-576-004	C	Cable, USB-A to USB-B, 2meter RoHS	48.00
H11576-ND	C	Cable Micro USB A-Std A	49.95

Accessories - Holsters and Handles

SKU	SKU Type	SKU Description	List (€)
805-679-001	A	Scan Handle, CN51	124.32
815-066-001	A	CN50 Holster, Model	86.00
815-089-001	B	Holster,Nylon,CN50/CN51 w/o Scan Handle	85.47
815-090-001	C	Holster,Nylon,CN51 with Scan Handle	91.02
815-092-001	N	Belt Holster, CN51	54.75

Accessories - Power Adapters

SKU	SKU Type	SKU Description	List (€)
213-029-001	C	Kit includes AC Power Adapter Kit (US, EU, UK, ANZ) & USB Cable	31.08
851-061-502	A	Univ Adptr w/Bead,12V 3.5x1.4mm, Level V (AC adapter for Desktop Single Dock & Quad Battery Charger. Requires country specific power cord.)	64.38
851-093-311	A	Desktop Power / Comm Adapter CN50/CN51 (Provides Desktop Charging and USB port. Requires Country Specific Power Cord. (For use Worldwide.))	106.56
852-073-001	C	Desktop USB Adapter, CN50/CN51 (Provides Desktop USB port (CN50/CN51) and charging (CN51 only; via USB).)	78.81

Accessories - Power Cords

SKU	SKU Type	SKU Description	List (€)
1-974027-025	A	AC Power Cord, Europe RoHS	11.10
1-974029-020	A	AC Power Cord, UK RoHS	11.10
321-471-002	C	AC Power Cord, Italy RoHS	11.10
321-501-002	C	AC Power Cord, Denmark RoHS	11.10

Accessories - Power Supplies

SKU	SKU Type	SKU Description	List (€)
851-082-205	C	Univ Supply R/A 2.5x5.5 FWC5012 CEC/RoHS (Right Angle Plug)	64.38
851-095-131	A	Univ Supply, 12V 48W, RA 2.5x5.5 Level V	67.71

Accessories - Replacement Parts

SKU	SKU Type	SKU Description	List (€)
203-899-001	C	CN50 Kit, Handstrap Replacement, (5pack)	86.00
203-900-002	C	CN50 Kit,Tethered Stylus, (5 pack)	48.00
213-008-001	C	KIT, HANDSTRAP REPLACEMENT, CN51 (5PCS)	154.29
213-024-001	C	KIT, HAND STRAP, STR LIMITER, CN51(5pcs)	154.29
213-025-001	C	kit, stylus, replacement, CN51 (5pcs)	86.58
346-069-054	C	Screen Protector, CK31/CN50, 5 Ea RoHS	67.71
346-069-104	B	CK31/CN50 Screen Protector,10 Ea RoHS	124.00
346-069-204	B	Screen Protector,CK31/CN50, 25 Ea RoHS	162.06
346-085-001	B	Screen Protector Kit CN51, 10 Each RoHS	125.43

Accessories - Snap-on Adapters

SKU	SKU Type	SKU Description	List (€)
850-573-001	C	CN50 Mag Stripe Reader, Endcap, ((Snap-on Adapter. Attaches to heel of CN50 series and provides magnetic stripe reader.)	367.00
850-578-001	C	CN50 Snap-on Adapter,RS232,,RoHS (Snap-on Adapter. Attaches to heel of CN50 series and provides RS232 cabled support from bottom of CN50. Adapter provides DB9M connector. Must order cable separately.	136.00
850-581-001	C	Snap-on Adapter, USB, CN50/CN51 (Snap-on Adapter. Attaches to heel of CN50 series and provides USB cabled support from bottom of CN50 series. Adapter provides HDB15M connector. Must order cables separately.)	135.42

Accessories - Storage Cards

SKU	SKU Type	SKU Description	List (€)
856-065-004	B	MICRO-SD CARD, 1GB, AF1GUDI, ROHS	84.36
856-065-005	C	MICRO-SD CARD, 2GB, AF2GUDI, ROHS	139.86
856-065-006	C	MICRO-SD CARD, 4GB, AF4GUDI, ROHS	219.78
856-065-007	C	Micro-SD Card, 8GB, AF8GUDI, RoHS	296.37

Accessories - Vehicle Dock Accys

SKU	SKU Type	SKU Description	List (€)
852-070-011	A	Vehicle Power Adapter, CN50/CN51 ((12 to 24 Volt Cigarette Lighter Adapter) Can be used with or without Vehicle Holder.)	112.11
871-037-001	B	Vehicle USB & Power Adapter, CN51. Requires Vehicle Holder (805-664-001).	140.97

Accessories - Vehicle Docks

SKU	SKU Type	SKU Description	List (€)
805-664-001	B	Vehicle Holder, CN50/CN51 (requires 805-611-001)	47.73

Accessories - Vehicle Docks & Accessories

SKU	SKU Type	SKU Description	List (€)
805-611-001	B	Consists of one 4 ž adjustable pivot arm with two 1 stainless steel balls and assembly hardware. Due to wide range of possible applications, this kit doesn’t include hardware for securing mount to vehicle.	134.31

Software - Catalog End Item

SKU	SKU Type	SKU Description	List (€)
454-034-001	Virtual	Client Lic, Intermec Connection Manager (Single Device Client License for Intermec Connection Manager. One license per device required, licenses are electronically distributed and managed. License includes 1 yr of Software Maintenance.)	49.95

Software - Enterprise Browser

SKU	SKU Type	SKU Description	List (€)
454-026-001	Virtual	Intermec Browser license for WEH6.5, WM6, CE6, WEC7, Win7 and similar OSes, includes 1 year of software maintenance. Do not order for Android or W10 IoT. For Android or W10 IoT, order BROWSER-001 instead.	105.00
IBMAINT-SFT1	Virtual	Software Maintenance, Enterprise Browser, 1 year. This license is for Enterprise Browser on WEH6.5, WM6, CE6, WEC6, WEC7, Win7 and related OSes. Do not order for Android or W10 IoT. For Android or W10 IoT order BROWSER-SFT1 instead.	18.00



IBMAINT-SFT3	Virtual	Software Maintenance, Enterprise Browser, 3 years. This license is for Enterprise Browser on WEH6.5, WM6, CE6, WEC6, WEC7, Win7 and related OSes. Do not order for Android or W10 IoT. For Android or W10 IoT order BROWSER-SFT3 instead.	51.42
--------------	---------	---	-------

Software - Honeywell Launcher

SKU	SKU Type	SKU Description	List (€)
LAUNCHERLN-001	Virtual	Honeywell Launcher license for WEH6.5, WM6, CE6, WEC7, Win7 and similar OSes, includes 1 year of software maintenance. Do not order for Android. For Android, order LAUNCH-001 instead.	42.00
LAUNCHER-SFT1	Virtual	Software Maintenance, Honeywell Launcher, 1 year. This license is for Honeywell Launcher on WEH6.5, WM6, CE6, WEC6, WEC7, Win7 and related OSes. Do not order for Android. For Android order LAUNCH-SFT1 instead.	9.99

Software - Launcher Maintenance

SKU	SKU Type	SKU Description	List (€)
LAUNCH-SFT1	Virtual	Software Maintenance, Launcher for Android, 1 year. Order this part number for use with CT50, D75e or CN51.	5.55

Software - Product

SKU	SKU Type	SKU Description	List (€)
238-000-002	Virtual	Conversion License, CN51 Android OS	81.03

Software - Software

SKU	SKU Type	SKU Description	List (€)
454-023-001	Virtual	License, Intermec Client Pack (Includes 1 year Software Maintenance. This License is delivered via e-mail, therefore the License recipient's e-mail address must be provided for sales order processing.)	229.10
LAUNCH-001	Virtual	Launcher License for Android OS. Includes 1 year of software maintenance. Order this part number for use with CT50, D75e or CN51.	42.00
PERSISTLN-001	Virtual	SW License for Session Persistence plus (Order 1 license per server. Ships via electronic fulfillment, license via email, therefore the license recipient's email address must be provided for sales order processing. First year of maintenance is included in	2897.10

Software - Software Licenses

SKU	SKU Type	SKU Description	List (€)
454-077-001	N	Upgrade License, CN51 Android 6	79.00
454-078-001	N	Conversion License, CN51 WEH 6.5 to Android 6	79.00

Software - Software Maintenance

SKU	SKU Type	SKU Description	List (€)
ICP-SFT3	Virtual	Intermec Client Pack Maintenance 3 YR (Customers must be on current version of Intermec Client Pack to subscribe to maintenance. Maintenance is not valid without an existing ICP license. Must purchase 1 maintenance contract per ICP license. Entitles custo	129.45

Software - Software v1

SKU	SKU Type	SKU Description	List (€)
CMANAGE-SFT3	Virtual	Intermec Connection 3yr SW Maint	33.30

Software - SW Maintenance

SKU	SKU Type	SKU Description	List (€)
CMANAGE-SFT1	Virtual	Intermec Connection Mgr SW Annual Maint (Single Device SW Maintenance for Intermec Connection Manager provides support and no charge upgrades. SW Maintenance entitles user to client software updates and support for 1 year. Use subject to Intermec terms a	19.98
ICP-SFT1	Virtual	Intermec Client Pack Maintenance 1 YR (Customers must be on current version of Intermec Client Pack to subscribe to maintenance. Maintenance is not valid without an existing ICP license. Must purchase 1 maintenance contract per ICP license. Entitles cust	53.28
PERSIST-SFT1	Virtual	Session Persistence Svr Maintenance 1YR (Customers must be on current version of Session Persistence Server to subscribe to maintenance. Maintenance is not valid without an existing SPS license. Must purchase 1 maintenance contract per SPS license. Entit	567.21

Honeywell Repair Services - Mobile Computer Service Contracts

SKU	SKU Type	SKU Description	List (€)
SVCCN51-2FC5	N	CN51, Full Comprehensive, 2 Day Turn, 5 Year DayOne	500.00

Global Services - Software Licenses

SKU	SKU Type	SKU Description	List (€)
-----	----------	-----------------	----------

Country Availability:

- [00]: Australia, Austria, Belgium, Bulgaria, Canada, Chile, Colombia, Cyprus, Czech Republic, Denmark, Dominican Republic, El Salvador, Estonia, Finland, France, Germany, Greece, Guatemala, Hong Kong, Hungary, Iceland, India, Indonesia, Ireland, Italy, Japan, Jordan, Latvia, Liechtenstein, Lithuania, Luxembourg, Malaysia, Malta, New Zealand, Netherlands, Norway, Panama, Peru, Poland, Portugal, Romania, Singapore, Slovakia, Slovenia, South Africa, Spain, Sweden, Switzerland, Thailand, Turkey, UAE, United Kingdom, United States, Venezuela
- [F1]: Australia, Canada, Dominican Republic, Guatemala, Peru, United States
- [U2]: Austria, Belgium, Bulgaria, Cyprus, Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Guatemala, Hungary, Iceland, Ireland, Italy, Jordan, Latvia, Liechtenstein, Lithuania, Luxembourg, Malta, Netherlands, Norway, Poland, Portugal, Romania, Singapore, Slovakia, Slovenia, Spain, Sweden, Switzerland, Turkey, UAE, United Kingdom, Venezuela

Note:

Global Services contracts availability varies per region.
Services such as Service Made Simple (SMS) are available in the EU, USA & Canada.
For countries outside of the EU, USA & Canada, please contract a Honeywell representative to confirm availability.

Prices are recommended resell prices only. HSM Distributors and Partners are free to define their own prices.

Honeywell official pricelist is the one regularly updated and published on this site.

All prices are subject to change without notice and will be confirmed upon reception of orders.

Although we have combined the legacy price guides, if you are ordering directly from Honeywell you will still need to continue with the existing process of placing split orders to each of the corresponding order management teams through your normal route.
We will provide further updates as this situation changes.
Thank you for your understanding and patience.

For more information on our products:
www.honeywellaidc.com

Honeywell Scanning & Mobility
9680 Old Bailes Road
Fort Mill, SC 29707
800.582.4263
www.honeywell.com

