

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 4 Wire 60A IEC309 980cm

PDM3460IEC309-980

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
--------------	--

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
Provided equipment	Installation guide

Physical

Colour	Black
Height	12.7 cm
Width	44.5 cm
Depth	40.6 cm
Net weight	6.09 kg

Input

Network frequency	60 Hz
Permissible voltage	200...240 V
Max line current	60 A

Output

Max current draw	60 A
Number of power socket outlets	1 IEC 309 60 A 3P + PE

Conformance

Product certifications	UL listed
------------------------	-----------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	12.7 cm
Package 1 Width	40.6 cm
Package 1 Length	44.5 cm
Package 1 Weight	6.64 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)