


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2017
© COPYRIGHT 1994 BY TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER PCN E-17-012564	28AUG2017	JA	DM
	A1	REVISED PER ECR-22-134367	13JUN2022	DM	IG
	A2	REVISED PER PCN-22-153032	19SEP2022	AM	IG
	B	REVISED PER PCN-23-192205	05FEB2024	RK	CB






FLANGE SEAL IS INTENDED FOR NON-PRESSURIZED FLUID SPLASH ONLY



2X THREADED INSERT
M6 X .500 DEEP
RECOMMENDED TORQUE:
62-88 IN-LB [7-10 N-m]



RECOMMENDED MOUNTING DETAIL

4 DATE CODE: MONTH IS REPRESENTED BY SEQUENTIAL ALPHA CHARACTERS. EX: A = JANUARY, YEAR IS REPRESENTED BY LAST NUMERICAL DIGIT. EX: 0 = 2010

3 MATERIAL: HOUSING,: PA66 GF15 (GRAY)
CAP: PA66 GF15 (BLACK)
GROMMET, GASKET: VMQ (RED-ORANGE)
INSERTS: STAINLESS STEEL

2. THIS RECEPTACLE MATES WITH DT06-12SA-XXXX PLUG. (XXXX = ALL MODIFICATIONS) CONSULT FACTORY FOR MODIFICATIONS.

1 FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERSTICS, SEE ENVELOPE DRAWING 0425-015-0000.

NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PN	DEUTSCH PN
DT04-12PA-LE05	DT04-12PA-LE05

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL O.D.	WIRE RANGE 1 [mm²] REF ONLY
16	.088 [2.23]	.145 [3.68]	14-20 AWG [2.5-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: in [mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±.025 [0.64]
4 PLC ±
ANGLES ±0° 30' 0"

MATERIAL 3

FINISH

DWN C. WOODRUFF 14MAR1994
CHK -
APVD -
PRODUCT SPEC 108-151009
APPLICATION SPEC 114-151009
WEIGHT 73g

TE Connectivity

NAME 3 WAY RECEPTACLE FLANGE MOUNT DT SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	C-DT04-12PA-LE05	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV B

1470-19 (3/13)

Downloaded from Arrow.com.