

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/22/25	SS

APPROVED: _____

DATE: _____ TITLE: _____




Recommended Land Pattern



Recommended Stencil

Solder Paste Thickness: 150um



SPECIFICATIONS:
Material: Brass, C3604
Plating:
Matte Tin over Nickel underplate overall
Electrical:
Current rating: 50A @Tested at 20°C
Mechanical:
Tightening Torque: 1.2N
Recommended PCB Thickness
.063 [1.6mm] Min. / .078 [2.0mm] Max.
Temperature Rating:
Operating temperature: −55°C to +150°C
Environmental:
Lead free, RoHS compliant

PACKAGED ON TAPE & REEL (SEE SHT 2 OF 2 FOR DETAIL)

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	.X	± .10	HOLES	Ø.X	±.10
	.XX	± .020		Ø.XX	±.015
	.XXX	± .015		Ø.XXX	±.010

DRAWN	LH	8/22/25
CHECKED	RC	8/22/25
APPROVED	SS	8/22/25

CONFIDENTIAL AND PROPRIETARY
This document contains confidential and proprietary information of Adam Tech. It is provided for design and reference purposes only. Reproduction, distribution, or disclosure to any third party is strictly prohibited without prior written consent. Adam Tech retains all rights, including international intellectual property rights.

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE
HIGH CURRENT TERMINALS THROUGH HOLE TYPE M4, WITH INTERNAL THROUGH-HOLE THREAD

SIZE	PART NO.	REV.
X	HCT-T-IT-M4-A-R	-


REF: - SCALE: NTS SHEET 1 OF 2

Downloaded from Arrow.com.


Rev	AWO #	Description	Date	Appr
		SEE SHT 1 OF 2 FOR REVISION		


APPROVED: _____


DATE: _____ TITLE: _____



Tape width	24 mm	Pull-of force 0,1 N - 1,3 N







	A	B	C	D	N	W1	W2	W3	W3
Tolerance	±.079 [2.00]	Min	Min	Min	±.079 [2.00]	+.079 [2.00]	Max	Min	Max
Tape width	12.992 [330.00]	.059 [1.50]	.504 [12.80]	.795 [20.20]	2.362 [60.00]	.961 [24.40]	1.197 [30.40]	.941 [23.90]	1.079 [27.40]

1Reel/750Pcs

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	.X	± .10	HOLES	Ø.X	±.10
	.XX	± .020		Ø.XX	±.015
	.XXX	± .015		Ø.XXX	±.010

DRAWN	LH	8/22/25
CHECKED	RC	8/22/25
APPROVED	SS	8/22/25

CONFIDENTIAL AND PROPRIETARY
This document contains confidential and proprietary information of Adam Tech. It is provided for design and reference purposes only. Reproduction, distribution, or disclosure to any third party is strictly prohibited without prior written consent. Adam Tech retains all rights, including international intellectual property rights.

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE
HIGH CURRENT TERMINALS THROUGH HOLE TYPE M4, WITH INTERNAL THROUGH-HOLE THREAD

SIZE	PART NO.	REV.
X	HCT-T-IT-M4-A-R	-

REF:	SCALE: NTS	SHEET 2 OF 2
-		

Downloaded from Arrow.com.