

Search within category

GO

BUY NOW

DESIGN / INSTALL



RGEJ1024URT

#10 AWG (6mm²) jumper, 24 in. (61 mm²) L, pre-terminated with one #10 (5.3mm) and one 1/4" (6.4mm)stud hole ring terminals to provide a bolt-on solution for grounding network equipment.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Length (In.)	24.00			
Length (m)	0.6			
Length (mm)	609.6			
Angle	Straight			
Application	Telecom/Data Center			
CSA Certified	Yes			
Color	Green/Yellow			
Conductor Size	#10			
Kit Contents	NA			
Overall Length (In.)	24.00			
Overall Length (mm)	600.0			
Product Type	Equipment Bonding Jumper			
UL Listed	Yes			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			