

Keyspan Mini DisplayPort to VGA/DVI/HDMI All-in-One Video Converter Adapter, 4K 30Hz HDMI, DP1.2, White, 6-in. (15.24 cm)

MODEL NUMBER: **P137-06N-HDV4KW**



Passive Mini DP to HDMI/VGA/DVI adapter connects your Mini DP or Thunderbolt 1/2 laptop to a VGA, DVI or HDMI display.

Features

Passive Adapter Connects a Mini DisplayPort Device to a VGA, DVI or HDMI Display No more carrying around separate adapters for various monitors, projectors and televisions. This Keyspan® Mini DP to HDMI/VGA/DVI adapter connects a VGA, DVI or HDMI display to the Mini DisplayPort or Thunderbolt 1/2 port on your Chromebook, MacBook, Microsoft Surface or other compatible laptop or tablet. Only one display can be connected at a time.

Simple All-in-One Solution for Displaying 4K Video on a Large Screen The P137-06N-HDV4KW is ideal for classrooms, lecture halls and anywhere else you may need to connect to a monitor. Just connect the converter between your laptop and a VGA, DVI or HDMI display. You no longer have to dig around in your laptop bag for the correct adapter to match the display.

Transmits Crystal-Clear Video up to 4K x 2K for Ultra HD Presentations This all-in-one unit features separate female HD15, DVI and HDMI ports. The HD15 port supports high-definition video resolutions up to 1920 x 1200, including 1080p. The DVI-I dual-link port supports HD resolutions up to 1920 x 1080 (1080p). The HDMI port supports Ultra HD 4K x 2K video (3840 x 2160) at 24/30 Hz, as well as 36-bit Deep Color (12 bits per channel). The HDMI port is backward compatible with non-4K displays.

Passive Adapter for Use with Dual-Mode DisplayPort Sources The P137-06N-HDV4KW is a passive adapter that requires the connected computer to support DisplayPort++ (DP++). This allows HDMI and DVI signals to be passed through. Check the documentation for your Mini DisplayPort source for compatibility.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female Mini DisplayPort or Thunderbolt 1/2 port. With its small size and built-in cable, the P137-06N-HDV4KW is recommended for stowing in your laptop bag and carrying to school or the office.

3-Year Warranty The P137-06N-HDV4KW is backed by a 3-year warranty, ensuring reliability and performance.

Highlights

- Multiple video outputs connect to most displays—no more carrying multiple adapters
- HDMI port delivers UHD quality at resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation
- Passive adapter requires connected computer to have DP++ port for signal pass-through

Applications

- Connect your laptop to an HDMI, VGA or DVI monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the PC or laptop in your office or home workspace

System Requirements

- Source device with Thunderbolt 1/2 output or Mini DisplayPort that supports DP++
- Display device with VGA, DVI or HDMI input

Package Includes

- P137-06N-HDV4KW Keyspan Mini DisplayPort 1.2 to VGA/DVI/HDMI All-in-One Converter Adapter, White
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332210630
Product Type	Video Adapter
Technology	DVI; HDMI; VGA/SVGA; DisplayPort
PHYSICAL	
Color	White
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	0.91 x 5.40 x 4.00
Shipping Dimensions (hwd / cm)	2.31 x 13.72 x 10.16
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL LINK (FEMALE)
Side B - Connector 2	HD15 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.