



AWVI00322522330JH0

Search by :

Part Number

Characteristics

Cross reference



NEW



Wire Wound-STD

Series Pdf



RoHSREACHCoC



Product detail

Structure	Wire Wound
L(mm) ±	3.2±0.2
W(mm) ±	2.5±0.2
T(mm) ±	2.2±0.2
Size Code (JIS/EIA)	3225/1210
Inductance(uH)	33
Unit	uH
Tolerance(±%)	5
Test Frequency(L)	2.52MHZ
Q Min	15
Test Frequency(Q)	2.52MHZ
SRF(MHz)Min	10
RDC(Ω)Max	1.4
Irms(mA)Max	280

Operating Temperature

−40℃~125℃



Products

- Power Inductor
- EMI-Common Mode Choke
- EMI-Bead
- RF-Signal Inductor
- RF-Passives/Antennas
- LAN Transformer
- Resistor & Current Sensor

Applications

- Automotive
- Industrial
- Server/DataCenter
- Communication
- Mobile and Tablet
- Computer/Laptop
- Consumer

Design Tools

- Simulation Tool
- Product Search Engine
- E-Catalogue

About Us

- Corporate Overview
- Corporate Milestones
- Core Technology
- Certificates & Awards
- Quality and Social Responsibility

Investor

[Financial Information](#)

[Corporate governance](#)

[Stakeholder Contacts](#)

News

[Media Center](#)

[New Products](#)

[Events](#)

[Product Notices](#)

Contact Us

[Contact Info](#)

[Contact Form](#)

[Join Chilisin](#)

[Terms of Use](#)

[Privacy policy](#)

[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisin. All rights reserved.