Part Number : 191930358
Product Description : VersaKrimp Ring Tongue Terminal for 3/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : K-390-38



Documents and Resources

Drawings

191930358_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 3/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755052480

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	34.668/g
Packaging Type	Carton
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	19.02mm max.
Wire Size (AWG)	3/0
Wire Size mm^2	95.00

Downloaded from Arrow.com.

Application Tooling

This document was generated on Apr 11, 2026

Downloaded from Arrow.com.