

# C-RCI 6/M6 - Ring cable lug

3240029

<https://www.phoenixcontact.com/us/products/3240029>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ring cable lug, yellow, 4 ... 6 mm<sup>2</sup>, M6

## Your advantages

- The sleeves are conically tapered to facilitate easy and correct insertion of the conductor
- The insulated ring cable lugs with plastic sleeve are hard-soldered and feature the 'EASY ENTRY' system

## Commercial data

Item number	3240029
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BH34
Product key	BH3421
Catalog page	Page 492 (C-3-2019)
GTIN	4046356452069
Weight per piece (including packing)	2.295 g
Weight per piece (excluding packing)	2.2 g
Customs tariff number	85369010
Country of origin	CN

# C-RCI 6/M6 - Ring cable lug

3240029

<https://www.phoenixcontact.com/us/products/3240029>




## Technical data

### Product properties

Product type	Connector
Product property	Halogen-free
	With “Easy Entry” system
	Brazed
	PA-insulated

### Dimensions

Dimensional drawing	
Width	12 mm
Sleeve length	32.7 mm
Length of the insulating material sleeve	14 mm
Maximum stripping length	9 mm
Distance from the center to the insulating material sleeve	12.7 mm
Min. material thickness	1 mm
Inner dimensions of the insulating collar	6.6 mm

### Internal dimensions

Internal diameter	6.5 mm
-------------------	--------

### Material specifications

Color	yellow (RAL 1018)
Material	Copper
Flammability rating according to UL 94	V2
Coating	tin-plated
Insulating material	PA
Components	halogen-free

### Mechanical properties

#### Technical data

Sleeve length	32.7 mm
---------------	---------

### Environmental and real-life conditions

#### Ambient conditions

Optimum ambient temperature (storage/transport)	20.00 °C 50.00 % Humidity (RH), store inside sealed original packaging. Avoid direct sunlight and heat.
Ambient temperature (operation)	-20 °C ... 105 °C

# C-RCI 6/M6 - Ring cable lug

3240029

<https://www.phoenixcontact.com/us/products/3240029>



Ambient temperature (assembly)	-20 °C ... 100 °C
Short-term temperature	100 °C

# C-RCI 6/M6 - Ring cable lug


3240029

<https://www.phoenixcontact.com/us/products/3240029>



## Drawings

Dimensional drawing



# C-RCI 6/M6 - Ring cable lug

3240029

<https://www.phoenixcontact.com/us/products/3240029>



## Classifications

### ECLASS

ECLASS-13.0	27400204
-------------	----------

### ETIM

ETIM 9.0	EC001052
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# C-RCI 6/M6 - Ring cable lug



3240029

<https://www.phoenixcontact.com/us/products/3240029>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)