



+ CONNECTORS
RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
SMB,75 OHM,JACK,R/A,PCB
Miniature Coax

5415895-1
TE Internal Number: 5415895-1

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Connector Interface SMB
Connector Style Jack
Mated Outer Diameter (Approximate) 4.75 mm [.187 in]
Impedance (Ω) 75
Connector & Contact Terminates To Printed Circuit Board

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings
JACK WITH PANEL GROUND, PCB, RIGHT ANGLE, 75 OHM, SMB
PDF (TIFF AVAILABLE)
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SMB
Connector Style Jack
Connector & Contact Terminates To Printed Circuit Board

Configuration Features
PCB Mounting Orientation Right Angle

Electrical Characteristics
Impedance (Ω) 75

Body Features
Body Material Brass
Body Plating Material Tin

Contact Features
Center Contact Plating Material Gold
Center Contact Material Brass
Connector Product Type Connector Assembly

Termination Features
Termination Method to PC Board Through Hole

Mechanical Attachment
Panel Attachment Style Front Mount

Dimensions
Mated Outer Diameter (Approximate) 4.75 mm [.187 in]

Packaging Features
Packaging Method Tray

Other
Dielectric Material PTFE
Additional Features Board Standoff, Pin Protection
Grade Commercial

PRODUCT COMPLIANCE



Statement of Compliance
Statement of Compliance
PDF

