



Part Number : [936030101](#)
Product Description : Heavy-Duty Connector Kit, 32 Pole, Series S-E Female-Male Inserts, Pg36 Extended Threaded Fitting Die-cast Aluminum Hood-Side Entry, Surface Mount Housing-Vertical, 2 Lever, Size 32B «77x62», Grey
Series Number : 93603
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7932.6763.0



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93603
Description	Heavy-Duty Connector Kit, 32 Pole, Series S-E Female-Male Inserts, Pg36 Extended Threaded Fitting Die-cast Aluminum Hood-Side Entry, Surface Mount Housing-Vertical, 2 Lever, Size 32B «77x62», Grey
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Kit Component Parts	Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 32B «77x62», Pg36 Extended Threaded Fitting, Grey, High Construction, Heavy-Duty Screw Terminal Insert, Male, 16-Pole, 16A, Numbered 1-16, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27», Heavy-Duty Screw Terminal Insert, Male, 16-Pole, 16A, Numbered 17-32, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27», Heavy-Duty Screw Terminal Insert, Female, 16-Pole, 16A, Numbered 1-16, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27», Heavy-Duty Screw Terminal Insert, Female, 16-Pole,

	16A, Numbered 17-32, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27», Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 32B «77x62», Pg36 Thread, Grey
Product Name	Heavy-Duty Connectors
UPC	887191866284

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	500V

Physical

Color - Cable Jacket	N/A
Component Size	32B «77X62»
Lock to Mating Part	Yes
Mounting Style	Surface Mount
Packaging Type	Bag
Thread Size	Pg36
Thread Type	(Pg)

Kit Component Parts

Description	Part Number
Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 32B «77x62», Pg36 Extended Threaded Fitting, Grey, High Construction	<u>936014383</u>
Heavy-Duty Screw Terminal Insert, Male, 16-Pole, 16A, Numbered 1-16, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»	<u>936010273</u>
Heavy-Duty Screw Terminal Insert, Male, 16-Pole, 16A, Numbered	<u>936010277</u>

17-32, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»	
Heavy-Duty Screw Terminal Insert, Female, 16-Pole, 16A, Numbered 1-16, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»	<u>936010263</u>
Heavy-Duty Screw Terminal Insert, Female, 16-Pole, 16A, Numbered 17-32, with Wire Protection, Silver (Ag) Plated Contacts, Size 16B «77x27»	<u>936010267</u>
Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 32B «77x62», Pg36 Thread, Grey	<u>936014323</u>

This document was generated on Sep 14, 2025