



Image coming soon

Part Number : 1301120119
Product Description : 100W Guard Quick-Open Vaprotex, Steel, Zinc Plated
Series Number : 130112
Status : Active
Product Category : Portable Lighting Accessories
Engineering Number : 1259

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Portable Lighting Accessories
Series	130112
Description	100W Guard Quick-Open Vaprotext, Steel, Zinc Plated
NEMA Configuration	N/A
Product Family	Lighting Accessories
Product Name	Woodhead
Type	Accessory
UPC	78678861347

Electrical

Lamp Wattage - Maximum	100W
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Quick Open, Steel
Height	N/A
Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Net Weight	415.944/g
Outlet	None
Packaging Type	Carton