

LP-ADAPTER Han DD




Image is for illustration purposes only. Please refer to product description.

Part number	09 16 000 9908
Specification	LP-ADAPTER Han DD
HARTING eCatalogue	https://harting.com/09160009908

Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	In the Han DD [®] crimp insert
	In the Han DD [®] module
	In the Han [®] DDD module (different electrical data: 7.5 A 160 V 2.5 kV 3)

Version

Gender	Male
	Female
Details	for PCB's up to 2.4 mm

Technical characteristics

Rated current	7.5 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

Material properties

Material (insert)	Polyamide (PA)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	2.49 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140572799
eCl@ss	27460201 PCB connector (board connector)
UNSPSC 24.0	39121415