



Part Number : 1301070039
Product Description : Watertite Wet Location Stringlight 100W 12/3 SOOW 3 Lamps Lead, 13.72m (45.0') Cord Length
Series Number : 130107
Status : Active
Product Category : Lamps and Lights
Engineering Number : 380310A



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130107
Description	Watertite Wet Location Stringlight 100W 12/3 SOOW 3 Lamps Lead, 13.72m (45.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Family	Stringlights
Product Name	Watertite
Type	String Lights
UPC	78678834330

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	12/3 SOOW
Cord Type - Secondary	14/3 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Steel
Height	457.20mm (18.000")
Lamp Type	A21
Length	13.72m (45.0')
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stringer
Outlet	None
Packaging Type	Carton

Socket Construction	Rubber Molded
---------------------	---------------

This document was generated on Mar 26, 2024