

## SEK CAB FLAT NSH RND AWG28/7 60P 30,48m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| Part number        | 09 18 060 7008                                                                        |
| Specification      | SEK CAB FLAT NSH RND AWG28/7<br>60P 30,48m                                            |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09180607008">https://b2b.harting.com/09180607008</a> |

### Identification

|               |                      |
|---------------|----------------------|
| Category      | System cabling       |
| Element       | Bulk cables          |
| Specification | Not assembled        |
| Type of cable | Copper cable (round) |

### Version

|                 |          |
|-----------------|----------|
| Cable length    | 30.48 m  |
| Number of cores | 60       |
| Core structure  | AWG 28/7 |

### Technical characteristics

|                              |                                                |
|------------------------------|------------------------------------------------|
| Impedance                    | 100 $\Omega$                                   |
| Limiting temperature         | -30 ... +75 °C unmoved<br>-20 ... +75 °C moved |
| Conductor resistance @ 20 °C | $\leq 216 \Omega/\text{km}$                    |

### Material properties

|                             |           |
|-----------------------------|-----------|
| Material (cable)            | PVC       |
| Colour (cable)              | Grey      |
| RoHS                        | compliant |
| ELV status                  | compliant |
| China RoHS                  | e         |
| REACH Annex XVII substances | No        |



Pushing Performance

## Material properties

|                            |    |
|----------------------------|----|
| REACH ANNEX XIV substances | No |
| REACH SVHC substances      | No |

## Specifications and approvals

|                |                   |
|----------------|-------------------|
| Specifications | UL 1581 Sec. 1061 |
|                | UL PLCC, CL2      |
| CE             | Yes               |

## Commercial data

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Packaging size                 | 1                                              |
| Net weight                     | 843.5 g                                        |
| Country of origin              | USA                                            |
| European customs tariff number | 85444993                                       |
| eCl@ss                         | 27061801 Data and communication cable (copper) |