



Actual



Family

Catalog Number: CC-NPT-34-G-2
Product ID: 7TAD105080R0015
UPC Number: 78621091580
EAN Number: 05415022257885
Status: A
Replacement Catalog: NCG-075LG-2X6.6

Multi-Hole Cord Grip Connector with 2 Openings, 3/4 Inch Thread Length 0.590 Inch/15mm, Cable Range 0.230 to 0.290 Inch, Nylon, Gray

- Sturdy cable sealing mechanism which results in superior strain relief.
- Compact size ensures quick and easy installation in cramped spaces
- Non-metallic construction provides excellent corrosion, chemical and impact resistance.

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Multi-Hole Cord Connectors
Special Features	Sturdy Cable Sealing Mechanism Which Results In Superior Strain Relief
Application	Ideal for Connections and Strain Relief in Cramped Spaces
Standard	UL E13938, CSA
Size	3/4 Inch
Conductor Range	2 Openings, 0.230 to 0.290 Inch
Material	Nylon
Color	Gray
Temperature Rating	-30 to +80 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	15.0mm
Suitable for cable diameter	5.842-7.366mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Light grey
Model	Straight
Operating temperature	-30-+80°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	8.25x5.25x4.25
Outer Quantity	100
Outer Dimensions (inches)	10.25x8.5x8.75
Weight Uom	7 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000375
Catalog Page	Available on Website
Instruction Sheet	TA02021-TB2

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com