



Part Number : [1300970269](#)

Product Description : Dust-Tight Strain Relief Wide Range Grip, 1-1/4" NPT, Straight Male, Cable Diameter 23.88-31.75mm (.940-1.250"), Approximate Break Strength 317.51kg (700 lbs)

Series Number : 130097

Status : Active

Product Category : Cable Grips

Engineering Number : 36515



Documents & Resources

Drawings

[1300970269_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130097
Description	Dust-Tight Strain Relief Wide Range Grip, 1-1/4" NPT, Straight Male, Cable Diameter 23.88-31.75mm (.940-1.250"), Approximate Break Strength 317.51kg (700 lbs)
NEMA Rating	Dust Tight
Product Name	Dust-Tight
Type	Strain Relief Grip
UPC	78678836515

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	317.51kg (700 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	23.88-31.75mm (.940-1.250")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Insulated	Yes
Material - Body	Zinc Plated Steel
Material - Grip	Galvanized Steel
Mesh Length	0.279m (11.00")

Number of Holes	N/A
O-Ring	N/A
Thread Size	1 1/4" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1-1/4" NPT	<u>1300990146</u>

This document was generated on Sep 10, 2025