

BBB14224B, Bare Copper Busbar, 24" Long, 36 Holes

By Burndy
Catalog # [BBB14224B](#)



Copper Busbar, 36 Holes, 24 in L, Can be used as a common ground point and power applications.

Features

- Bare Copper Busbar
- UL Listed for Grounding
- Many sizes and hole patterns available

Application

For Used As A Common Ground Point And Power Applications

General

Catalog Number	BBB14224B
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Holes	36
Sub Brand	BUS BAR
Type	BBB
UPC	781810489321
UPC 14 Digit GTIN	00781810489321

Dimensions

Dimension - Bar Length inch	24 in
Dimension - Bar Length mm	610 mm
Dimension - Bar Thickness inch	0.25 in
Dimension - Bar Thickness mm	6 mm
Dimension - Bar Width inch	2 in
Dimension - Bar Width mm	51 mm

Dimension - Hole Size inch	0.28 in
Dimension - Hole Size mm	7 mm
Dimension - Width fraction	2 in
Dimension - Width inch	2.00 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	90

Product Assets

- [Brochures - Grounding Busbars - Complete Product Guide](#)
- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10103867](#)
- [Specifications - BBB14224B](#)