TE Connectivity: Every Connection Counts
© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

SCREENED

✔ Active

PRODUCT DRAWING
English

3D PDF

TE CONNECTIVITY (TE)

208M908-19A04

208M908-19A04
TE Internal Number: 738155-000
Alias ID: 6-1195762-0

Not EU RoHS or ELV Compliant
Find Compliant Alternatives

Product Drawings

Braid Tail Backshell
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Catalog Pages/Data Sheets

5-1654025-5_sec6_Adapters
PDF
English

Product Specifications

Downloaded from Arrow.com.

Product Specification

General Harness Repair Manual
PDF
English

General Information Package For Solid, Spin Coupling And Shielded Adapters
PDF
English

Adapter Finish Specifications
PDF
English

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Termination Device Type	**Magneform Ring**
	Style	**Shielded Boot**
Body Features	Adapter Plating Material	**Cadmium per SAE AMS-QQ-P-416, Type II, Class 3**
	Adapter Entry Size	**04**
	Material	**Aluminum**
Dimensions	Cable Diameter Range	**32 – 51 mm [125 – 2 in]**

Product Compliance

Statement of Compliance
PDF

VIEW ALL PRODUCT COMPLIANCE

Downloaded from Arrow.com.