



## YBM8CT2

by Burndy  
Catalog ID: YBM8CT2

Prop 65 Notice

Cu Compression Flag-Type Ring Terminal, 8 AWG flex, 1/4" stud, Tin plated

### Product Details

#### General

Connector Type	Terminal - Ring
Die Index	54
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810054697

#### Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.07 in
Dimension - N inch	0.29 in
Dimension - Outside Diameter inch	0.32 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	90 Degree

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	8 (37/#24)
Conductor - Copper Flex I Size	8
Conductor - Copper Flex K Size	8
Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)