








PCB layout, component side (thickness 1,6 min)



Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200301.

0955 256 6622 333	2	4-40 UNC	Black insulator	Samples
0955 256 3622 741	1			
0955 256 6622 741	2			
0955 256 7622 741	3			
0955 256 3621 741	1	M3	Reel packaging (140 connectors)	
0955 256 6621 741	2			
0955 256 7621 741	3			
Part number	PL	Screw lock	Index designation	

		All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.								
							Sub.								
		All rights reserved		Created by ZHUANGJ		Inspected by LUOK		Standardisation HOFFMANN		Date 2018-11-16		State Final Release			
		Department EL PD		Title D-Sub angled standard SMT 15-pole female ass with screw lock								Doc-Key / ECM-Nr. 100684632/UGD/001/C 500000141375			
HARTING Electronics GmbH D-32339 Espelkamp				Type TB		Number 0955256X62X						Rev. C		Page 1/1	