



R89F-DS1238H

DC Axial fan, plastic blade, frame 120x38, high speed

Specifications

Size	120 x 120 x 38 mm
Operating voltage at DC	20.4-27.6 V
Rated current	0.5 A
Rated power	12 VA
Rated rotational speed	3600 r/min
Maximum flow rate	3.88 m³/min
Maximum static pressure	135 Pa
Noise emission	49 dB(A)
Set content	Fan only

Downloads

CAD Library



**EAC Mark removal
Discontinuation Notice**
EN PDF 221 KB



**R89F
Datasheet**
EN PDF 5.37 MB



**R89F Axial Fans
Brochure**
EN PDF 5.68 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 5 July, 2025. Click here for [terms of use](#).



INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU