



PART FINDER

FIND NOW

Find faster what you're looking for!

Always a good connection
Always a good connection

Product Overview

Connectors

- o Customer specific solutions
- o D SUB
- o D SUB accessories
- o D SUB cover
- o DVI
- o Centronics
- o IDC
- o Modular
- o USB
- o USB 3.0 + USB 3.1
- o IEEE 1394
- o Power supply
- o DIN 41612
- o DIN 41617
- o Mini DIN
- o IC Socket
- o **Pin and female header**
- o LED connectors
- o Jumper
- o Connector sleeves
- o Solder terminals
- o Test terminals
- o Terminal Blocks
- o Memory Card connectors
- o FFC / FPC connectors
- o Micro-Miniature
- o Keystone Jack
- o Gender Changer
- o Modular Plug
- o Waterproof parts

Thermal management

Cable assembly

Capabilities



download
technical drawing



download
Product Change Notification



3D view

Pin and female header

A-SL200-EG-G05MR1

Pin-&female-header
pin-header single row SMT
05pins spacing 2,00mm
straight stamped contacts
4,00mm Au reel

Part number:	A-SL200-EG-G05MR1
product group:	Pin-&female-header
style:	pin-header
contact type:	SMT
pin count:	5
spacing in mm:	2,00
current rating:	1,5A
version:	single row
contact length:	4,00mm
contact direction:	straight
plating:	Au
contact machining:	stamped contacts
packaging:	reel
process:	SMT
insulator:	PA6T UL94V-0



ASSMANN WSW components
on electronics 2016 in Munich

Visit us at the Electronica 2016 in
Munich

November 8 - 11, 2016, Hall B2,
Booth 560

[MORE NEWS](#)



Company Film

Watch our company video!

[START WATCHING](#)

Contact

1840 W. Drake Drive, Suite 101
Tempe AZ, 85283, USA
+1 (480) 8977 001
info@assmann-wsw-usa.com

[TO CONTACT](#)

