


AFCI PART NO.

10123461-R0035YYLF

WIRING LIST			
P1		P2	
1	—	1	
2	—	2	
3	—	3	
	—		
10	—	10	
11	—	11	
12	—	12	



NOTES:

1. MATERIAL: SEE BOM ON SHEET 1.
2. THIS DIMENSION IS A FINISHED PRODUCT LENGTH.
3. ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST.
4. UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE TESTED:
HI-POT: DC 300V/10ms
DIELECTRIC RESISTANCE: 10M Ohms MIN.
CONNECTION RESISTANCE: 4 Ohms MAX.
5. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

6. LABEL SHOULD BE PRINTED WITH BLACK TEXT AS SHOW BELOW:

INPECO
561810020.0

1	EA	ADHESIVE LABEL: W=25mm, COLOR:WHITE, PRINT BLACK			3
A/R	FT	FLAT CABLE: UL2678, 0.635PITCH, 30AWG, 12PIN, COLOR:GRAY			2
2	EA	IDC CONNECTOR: 1.27PITCH, 2X6PIN, 10u" Au PLATING, COLOR:BLACK			1
Q'TY	UNIT	DESCRIPTION			ITEM
mat'l. code		surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family
ltr		ecn no	dr	date	title
A		/	Harry	03/08'13	1.27PITCH IDC CABLE ASSEMBLY
B		N-24535	Carl	07/20'16	
					scale N/A
					dwg no
					sheet 1 of 1
					size
					10123461
					A3
					type
					Customer
					Drawing
sheet	revision	B			
index	sheet	1			

PDS: Rev :B

STATUS: Released

Printed: Jul 29, 2016