



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND / OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.





**ADHESIVE BACKING:**

- \*[-A] RUBBER BASED ADHESIVE PRESSURE SENSITIVE FOAM TAPE 0.04 (1.0) THICK WITH A PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.28 lbs (127g) MAX. WEIGHT ON A CLEAN DRY SMOOTH SURFACE.
- \*[-AT] ACRYLIC BASED ADHESIVE PRESSURE SENSITIVE FOAM TAPE 0.04 (1.0) THICK WITH A PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.28 lbs (127g) MAX. ON A CLEAN DRY SMOOTH SURFACE.
- \*[-AV] HIGH BOND ACRYLIC BASED ADHESIVE PRESSURE SENSITIVE FOAM TAPE 0.04 (1.0) THICK WITH A PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.56 lbs (254g) MAX. ON A CLEAN DRY SMOOTH SURFACE.

| PANDUIT PART NO. *               | REC'M FASTENER             | USE WITH THESE CABLE TIE CROSS SECTIONS | WEIGHT lbs / 100 (g) / pcs |
|----------------------------------|----------------------------|-----------------------------------------|----------------------------|
| SGABM20-A<br>ABM20<br>PAM075NY-A | RUBBER ADHESIVE            | M, I,<br>SG100M, SG150I                 | 0.142<br>(64.4)            |
| SGABM20-AT<br>ABM20B             | ACRYLIC ADHESIVE           |                                         |                            |
| SGABM20-AV                       | HIGH BOND ACRYLIC ADHESIVE |                                         |                            |

**NOTES**

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
  2. PRODUCT IS SUPPLIED IN STRIPS OF TWO.
  3. [-A] MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 120°F (49°C).
  - [-AT] MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 180°F (82°C).
  - [-AV] MOUNT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 200°F (93°C).
- SCALE: FULL



**DIMENSIONS IN BRACKETS ARE METRIC [mm]**

CAD FILENAME/LAYERS

G03150FB\_PB\_SGABM20\_00B

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

**ADHESIVE BACKED MOUNT - SUPER GRIP  
COMPATIBLE (SGABM20-A, -AT, -AV);  
(ABM20, 20B); (PAM075NY-A,)**

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
[.X] ±0.05 (1.3) [XXX] ±0.010 (0.25)  
[.XX] ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE  
PROJECTION.

DRAWN BY  
**JAD**

MAT'L:

SCALE  
**2X**

DATE  
**6/12/06**

**NYLON 6/6**

DRAWING NO.  
**GB3150FB**

DWG  
**A**  
SIZE

|     |         |      |     |                              |          |     |      |     |  |
|-----|---------|------|-----|------------------------------|----------|-----|------|-----|--|
| OOB | 11-6-09 | TMSA | SMY | ADDED PART NUMBER SGABM20-AV | GB3150FB | OOB | KW   |     |  |
| REV | DATE    | BY   | CHK | DESCRIPTION                  | ECN      | - R | CUST | SUP |  |