




APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/03/11	

**SPECIFICATIONS:****Material:**

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Phosphor Bronze

**Plating:**

Tin over Copper underplate overall

**Electrical:**

Voltage rating: 600 V

Current rating: 2~4P: 13A, 6~10P: 11A

Dielectric withstanding voltage: 5000 VAC for 1 minute

Temperature Rating:

-55°C to +105°C

**Environmental:**

Lead free, RoHS compliant.

Positions: 02 thru 10

A= .250 [6.35] x No. of Positions + .050 [1.27]

B= .250 [6.35] x No. of Spaces

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE MM [INCHES]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ± .10 ØX ± .10  
.XX ± .020 ØXX ± .015  
.XXX ± .015 ØXXX ± .010

## APPROVALS

DRAWN TW 11/03/11

CHECKED AY 11/03/11

APPROVED

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: WIRE TO BOARD, FEMALE, 6.35mm PITCH

WITH POLARIZING, SINGLE ROW TYPE

SIZE X PART NO. DME-F-XX-S-P-S-V0

REV. -

REF: S00123T SCALE: NTS SHEET 1 OF 1

**RoHS  
COMPLIANT**