


PRODUCT NUMBER
10177780-Z0120YYLF

ANGULAR	±5°
63 < L	±0.5
16 < L ≤ 63	±0.4
4 < L ≤ 16	±0.3
L ≤ 4	±0.2
UNSPECIFIED TOLERANCE	






NOTE:
1.ELECTRIC CHARACTERISTIC:
a. 100% OPEN AND SHORT TEST, INTERMITTENC, INSULATION WITHSTAND VOLTAGE TEST.
b. INSULATION RESISTANCE: ≥10MΩ, DC 300V,0.01S
c. CONDUCTOR RESISTANCE: <3Ω .
2. TRANSFERRING SPEED : 10Gbps
3. INSERTION LOSS : <-13db@10Gbps.
4.BENDING TEST : LEAD 200G,±90°,1000CYCLES.



外模编号:HK-2022-11-040
内模编号:KD202408081

接线表



Qty	Unit	Description	Item
/	M	COPPER FOIL W=5MM	9
/	KG	INNERMOLDING PE	8
/	KG	OVERMOLD TPE 85A	7
2	EA	WIRE CLIP PE	6
/	KG	UV GLUE	5
/	EA	SHIELDING SHELL (BOTTOM+TOP)	4
1	EA	USB Type C PLUG WITHOUT EMARK	3
1	EA	USB Type C PLUG WITH EMARK	2
/	M	USB4 CABLE {(36AWGX1C+SCM)X8C+(34AWGX2C+30AWGX1C+36AWGX2C+EA)+36AWGX2C}+CT BLACK TPE OD:2.6	1

ltr	ecn no	dr	date
A	/		03/06'26

dr	Steven	03/06'26
engr	Steven	03/06'26
chr	Tim Yao	03/06'26
appd	Tim Yao	03/06'26

mat'l. code
surface ISO 1302
tolerance ISO 406 ISO 1101
tolerances unless otherwise specified
angles
linear
projection
MM
scale N/A
product family: Cable Assembly
title: TYPE C TO C SMALL OD CABLE ASSEMBLY
dwg no 10177780
sheet 1 of 1
size A3
type Customer Drawing
sheet index
revision A
sheet

form: A3_2016_02_24

PDS: Rev :A STATUS: Released Printed: Mar 09, 2026

Downloaded from Arrow.com.