

Components

> [Connectors](#)

> [Relays](#)

▼ [Touch Panels](#)

> [4-Wire](#)

> [5-Wire](#)

> [7-Wire](#)

> [Multi-input](#)

> [KVM Switches](#)

> [Thermal Printers](#)

> [Input Devices](#)

> [Wireless Modules](#)

> [DC/DC Converters](#)

N010-0551-T642

RoHS compliant

**Type** 7-Wire  
**Category** Standard  
**Status**  Active  
**Datasheet**  TBA  
**Drawing**  [N010-0551-T642 \[456KB\]](#)  
**Description** Standard 7-Wire Touch Panel, 10.4 inches

| Specifications               |                       |
|------------------------------|-----------------------|
| Size                         | 10.4                  |
| Input Type (F=Finger, P=Pen) | P/F, light touch type |
| Cable Exit                   | Right                 |
| Cable Length                 | 100mm                 |
| Outer Dimensions (XxY)       | 228.20 x 175.40mm     |
| Transparent Area (XxY)       | 217.10 x 164.40mm     |
| Active Areas (XxY)           | 212.20 x 159.40mm     |

Notes: 1.8mm glass

We're Here to Help

How to Buy

- [Sales contacts](#)

Support Info

- [Technical / sales support](#)

[Top of Page](#)

Products

[Semiconductor Solutions](#)  
[Components](#)  
[Scanners, Printers](#)  
[Computing](#)  
[Telecommunications](#)

Services

[Across EMEA](#)

Help and Support

[Across EMEA](#)

Most Popular

[Scanners](#)  
[Relays](#)

Country Selector

Europe, Middle East and Africa  
[Change](#)

