




Part Number : [1300060034](#)
Product Description : Mini-Change A-Size Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 18 AWG, Yellow TPE Cable, 1.0m (3.28') Length
Series Number : 130006
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 104006K03M010



Documents and Resources

Drawings
[1300060034 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 18 AWG, Yellow TPE Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended
UPC	78678808506

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	5.6A
Voltage - Maximum	300V

Physical

Cable Diameter	7.14mm (.281")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None

Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	144.000/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	18

This document was generated on Dec 29, 2025