Specifications







Eaton CL0608-2-100TR-R

Eaton CL0608 inductor, 100 nH, 0.89 mΩ resistance, Two-phase

General specifications	
PRODUCT NAME	Eaton CL0608 inductor
CATALOG NUMBER	CL0608-2-100TR-R
UPC	051712545402
PRODUCT LENGTH/DEPTH	10.3 mm
PRODUCT HEIGHT	6.05 mm
PRODUCT WIDTH	8 mm
PRODUCT WEIGHT	2.364 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Downloaded from Arrow.com.

Product specifications

TYPE	Multi-phase coupled inductor
MOUNTING	SMT
PHASE	Two-phase
ISAT	38 A
PACKAGE QUANTITY	500
MATERIAL	Ferrite
CONTACT CONFIGURATION	Four-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.89 mΩ
TERMINALS	Four
INDUCTANCE	100 nH
SERIES	CL0608

Resources

CATALOGS	Magnetics short form catalog
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CL0608-2-100TR-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.

Downloaded from Arrow.com.