


HONEYWELL PART NUMBER
111SM602-H4
PRODUCT CODE TYJ9012

REV	DOCUMENT	CHANGED BY	CHECK
8	0038225	PRS 04APR08	BLR



NOTE -
① - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375^{±.002} CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO. PR - 3451

REPLACES -

CHARACTERISTICS
OPERATING FORCE - - - - 7 OZ MAX
RELEASE FORCE - - - - - 2 OZ MIN
PRETRAVEL - - - - - .219 MAX
DIFFERENTIAL TRAVEL - - - .025 MAX
OVERTRAVEL - - - - - .030 MIN

ELECTRICAL DATA			
CONTACT ARRANGEMENT SPDT			
30 VOLTS DC RATING			
		SEA LEVEL	50,000 FT
INDUCTIVE	3 AMP	2.5 AMP	
RESISTIVE	5 AMP	5 AMP	
MAXIMUM INRUSH 24 AMP			
APPROVALS	KEMA, CE	5A, 250V ~ T85 1E4	CE
	UL, CSA	5A, 250 VAC	UL

DESIGN UNITS: INCH			
TOLERANCES UNLESS NOTED:			
NO PLACE	X	±	-
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	-
ANGLES		±	-
THIRD ANGLE PROJECTION			

DRAWN	VK	29OCT 07
CHECK	RJ	29OCT 07
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		
RASTER		

Honeywell			
TITLE SWITCH - BASIC			
SIZE	TYPE	DRAWING NAME	REV
B	I	111SM602-H4	8
SCALE	-	WEIGHT .008 LB MAX	SHEET 1 OF 1