




Home > 3050-B-440-B



Swage Standoffs

Model: 3050-B-440-B

Select Finish

-0 No Plate

Select Finish

-0 No Plate

RFQ

Choose a CAD format

Download CAD

View 3D Model

View 2D Drawing

View Spec Sheet

Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 1/4". The thread for this part is 4-40 and length is 7/16".

SWAGE TOOLING		
±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

PDF Catalog

RAF_catalog_0097.pdf

Thread	4-40
O.D.	1/4"
Shape	Round
Length (L)	7/16"
Material	Brass
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.188"
Thread Clearance	0.150"
Finish	-0 No Plate

RAF ELECTRONIC
HARDWARE

In 2008, RAF joined with MW Industries Inc., www.mw-ind.com, to become the nation's leading supplier of electronic hardware components to a variety of industries, including computers, telecommunications, medical, entertainment and military/aerospace.

Technical Information

- Electronic Hardware Components
- Engineering Data
- Capabilities Brochure
- Services
- Distributors

Company

- RAF Quality Management
- Industry Links
- What's New
- News
- About
- Contact
- Careers

Contact Us

95 Silvermine Rd.
Seymour CT 06483

Find Us

