



Representative Image

Catalog No. TC121-TB**Description: PUSH-IN MNT CLAMP .44X.41IN NAT NYL****UPC No 5414363075028****Home > Wire & Cable Management > Ty-Rap > Cable tie mounts**

Push-In Premountable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 11.30mm (0.445 Inches), Height of 10.54mm (0.415 Inches), Clip In Mounting Method

Descriptors

Category	Cable tie mounts
Special Features	Snap-In Premountable base for securing wire bundles in cabinets maintains the attractive external appearance of the equipment housing - Snap-Cap.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Push Mount
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Width	11.3 mm
Width	0.45 inch
Height	10.54 mm
Height	0.42 inch
Type of fastening	With insert clip
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour