

SERIES COM1

FEATURES


- ULTRA SMALL PACKAGE OF 3.2 x 2.5 x 1.0mm TYPICAL
- LOW SUPPLY VOLTAGE OF 1.8 AND 2.5 VDC AVAILABLE
- STANDBY FUNCTION
- LEAD FREE / RoHS COMPLIANT

SPECIFICATIONS


SERIES		COM118	COM125	COM13
FREQUENCY RANGE		1.544 MHz TO 60.000 MHz		
FREQUENCY STABILITY **		COM11810 : ±100 ppm	COM12510 : ±100 ppm	COM1310 : ±100ppm
		COM11805 : ±50 ppm	COM12505 : ±50 ppm	COM1305 : ±50ppm
		COM118025 : ±25 ppm	COM125025 : ±25 ppm	COM13025 : ±25ppm
OPERATING TEMPERATURE RANGE		-10°C TO +70°C (-40°C TO +85°C AVAILABLE)		
STORAGE TEMPERATURE RANGE		-55° C TO +125° C		
INPUT	VOLTAGE	+1.8 VDC ±5%	+2.5 VDC ±5%	+3.3 VDC ±10%
	CURRENT (MAX)	1.544 MHz TO 9.99MHz: 5 mA MAX 10.00 MHz TO 31.99 MHz: 6 mA MAX 32.00 MHz TO 60.00 MHz: 15mA MAX	1.544 MHz TO 9.99MHz: 6 mA MAX 10.00 MHz TO 31.99 MHz: 8 mA MAX 32.00 MHz TO 60.00 MHz: 20mA MAX	1.544 MHz TO 9.99MHz: 7 mA MAX 10.00 MHz TO 31.99 MHz: 10 mA MAX 32.00 MHz TO 60.00 MHz: 20mA MAX
	SYMMETRY	40 TO 60% AT 50% VDD (45 TO 55% AVAILABLE)		
OUTPUT	RISE / FALL TIME	5 ns MAX		20 ns MAX
	LOGIC "0" LEVEL	VCC X 0.1 V MAX		
	LOGIC "1" LEVEL	VCC X 0.9 V MIN		
	LOAD	15 pF (HCMOS)		
ENABLE/DISABLE FUNCTION		PIN 1: HIGH OR OPEN PIN 3: OSCILLATION PIN 1: LOW PIN 3: HIGH IMPEDANCE		
START UP TIME		10 ms MAX		
STANDBY CURRENT		10 µA MAX		

** INCLUSIVE OF 25°C TOLERANCE, OPERATING TEMPERATURE RANGE, VOLTAGE OR LOAD CHANGES, AGING, SHOCK AND VIBRATION. CONSULT FACTORY FOR TIGHTER STABILITY OPTIONS.


OUTLINE DRAWING



REFLOW SOLDERING PROFILE



CARRIER TAPE DIMENSIONS



PACKAGING

178 mm REEL DIAMETER, 8mm TAPE WIDTH, 4mm PITCH
QUANTITY: 1000 PIECES PER REEL

PART NUMBERING SYSTEM

SERIES	SUPPLY VOLTAGE	FREQUENCY STABILITY	FREQUENCY	EXTENDED TEMPERATURE	DUTY CYCLE	TAPE & REEL
COM1	18 1.8V 25 2.5V 3 3.3V	10 ±100 PPM 05 ±50 PPM 025 ±25 PPM	IN MHZ	EXT	T 45% TO 55%	TR

EXAMPLES: COM1305-25.000-EXT-T-TR

Raltron Electronics Corporation 10651 NW 19th St. Miami, Florida 33172 U.S.A.

Tel: 305-593-6033 Fax: 305-594-3973 e-mail: sales@raltron.com Internet: <http://www.raltron.com>