





B	30 u"	HARD TRAY	WITH	2357798-6
	8 u"	TAPE & REEL	WITHOUT	2357798-4
	8 u"	TAPE & REEL	WITH	2357798-3
	8 u"	HARD TRAY	WITH	2357798-2
	8 u"	HARD TRAY	WITHOUT	2357798-1
	MATING ZONE PRECIOUS PLATING	PACKAGE	CAP	P/N



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C


C

B

B

A

A





REFERENCE P.C. BOARD LAYOUT
G: GROUND


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	TE Connectivity		
DIMENSIONS: mm		CHK HOPE LU 10OCT2019			
		APVD HOPE LU 10OCT2019	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE		
		PRODUCT SPEC 108-32658			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-115003	SIZE A2	CAGE CODE 00779	DRAWING NO C-2357798
MATERIAL - SEE NOTE 1		WEIGHT - SEE NOTE 2	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 6	REV B

WITHOUT PICK UP CAP
2357798-1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SECT. D-D
(SCALE 2:1)
(CONNECTOR NOT SECTION)



DETAIL C
(SCALE 2:1)





SECT. E-E
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	 TE Connectivity		
DIMENSIONS: mm		CHK HOPE LU 10OCT2019			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HOPE LU 10OCT2019	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE		
0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3°		PRODUCT SPEC 108-32658			
MATERIAL -		APPLICATION SPEC 114-115003	SIZE A200779	CAGE CODE C-2357798	RESTRICTED TO -
FINISH -		WEIGHT -	DRAWING NO C-2357798		
SEE NOTE 1		SEE NOTE 2		SCALE 1:1	SHEET 3 OF 6
		CUSTOMER DRAWING		REV B	


WITH PICK UP CAP
2357798-2&6

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SECT. C-C
(SCALE 2:1)



DETAIL E
(SCALE 4:1)



SECT. D-D
(SCALE 2:1)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	 TE Connectivity						
		CHK HOPE LU 10OCT2019							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HOPE LU 10OCT2019	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE					
			PRODUCT SPEC 108-32658						
			APPLICATION SPEC 114-115003						
		MATERIAL -	FINISH -	SIZE A2	CAGE CODE 00779	DRAWING NO C-2357798	RESTRICTED TO -		
		SEE NOTE 1	SEE NOTE 2	CUSTOMER DRAWING			SCALE 1:1	SHEET 4 OF 6	REV B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


DIRECTION OFF TOP OF REEL

REEL WITH PICK UP CAP
2357798-3


POS. NO. 1




DETAIL F
(SCALE 4:1)



SEE DETAIL F



WEEDING THE COVER TAPE
AROUND THE OUTER
PERIPHERY IN
A TURN.
165°~180° PEELING ANGLE








CONNECTOR DETAIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	TE Connectivity		
DIMENSIONS:		CHK HOPE LU 10OCT2019			
mm		APVD HOPE LU 10OCT2019	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-32658			
0 PLC ±1		APPLICATION SPEC 114-115003	SIZE A200779		
1 PLC ±0.3		WEIGHT -			
2 PLC ±0.15		CUSTOMER DRAWING	DRAWING NO C-2357798		
3 PLC ±0.050		SCALE 1:1			
4 PLC ±0.0250		SHEET 5 OF 6			
ANGLES ±3°		REV B			
FINISH -					
MATERIAL -					
SEE NOTE 1					
SEE NOTE 2					

REEL WITHOUT PICK UP CAP
2357798-4

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC	24JUN2019 10OCT2019 10OCT2019	TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3°	108-32658 APPLICATION SPEC 114-115003	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE	SIZE A200779	CAGE CODE C-2357798
MATERIAL - SEE NOTE 1	FINISH - SEE NOTE 2	WEIGHT - CUSTOMER DRAWING	RESTRICTED TO -	SCALE 1:1	SHEET 6 OF 6
				REV B	