

Part Number : 190380007

Series Number : 19038

Product Category : Quick Disconnects

Product Description : InsulKrimp Snap Receptacle, for 14-16 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm

Status : Active

Engineering Number : BRB-2156

Documents & Resources

Drawings

Drawing 190380007_sd.pdf

3D Models and Design Files

3D Model 190380007_stp.zip

Specifications

Product Specification PS-19902-011-001.pdf

Product Specification PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19038
Description	InsulKrimp Snap Receptacle, for 14-16 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm
Comments	Fits Male Plug size 3.96mm
Product Family	Snap Plugs and Receptacles
Product Name	InsulKrimp
Type	Snap Receptacle
UPC	800753048713

Agency

CSA	LR18689
UL	E152602

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	PVC
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	1.123/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	4.064 μ m
Plating min - Termination	4.064 μ m
Tab Thickness	N/A
Tab Width	N/A
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.81mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	1.00-2.50

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640012100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640052100</u>

This document was generated on Jul 28, 2024