


Specifications			Notes	Revision History						
Description	Value	Unit		Version	Description		Date	Approved		
Technology	Piezo		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		10/21/2013	J.S		
Resonant Frequency	2,048	(Hz)								
Rated Voltage	10	(V)								
SPL @ 10cm	80	(dBA)								
Capacitance	24,000	(pF)								
Mount Type	Thru-hole									
Voltage Range	1 ~ 40	(V)								
Max Rated Current	7	(mA)								
Housing Material	NORYL									
Operating Temperature	-20 ~ +80	°C								
Storage Temperature	-20 ~ +80	°C								
Weight	2	(g)								
				Drawn by		Date	Checked by	Date	Approved by	Date
				A.B.		10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
			Piezo Transducer			TP222010-1				