

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	45.6[CFM]
Max. Air Flow:	1.29[m3 per min]
Max. Static Pressure:	1.17[In H2O]
Max. Static Pressure:	290[Pa]
Fan Speed:	11000[RPM]
Noise:	52[dB]
Life Expectancy:	60 degrees C 40,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.2[V]
Mass:	95[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active

PWM Speed Control Fans